

# AP65


## LABEL APPLICATOR

# TOWA

No holes or special slits required in liner!  
**Mech-sensor** (exclusive label edge detector)  
mechanically senses label length.

SPARKS OF NEW TECHNOLOGY  
MECHANICAL-SENSOR  
WITH STRIKING NOVELTY

Just set the label roll, and you are ready to go!  
The Mech-Sensor on AP65 adjusts  
the label strokes automatically.



### Features:

- Mech-Sensor automatically detects leading edge of label, provides accuracy in dispensing.
- Requires no holes or special slits in liner. (exclusive label edge detector, mechanically senses label length)
- Loads fast and easy (easy side loading) ■ Needs no special cartridges, or cassettes.

[www.ap65.com](http://www.ap65.com)


PAT. P.

# AP65 LABEL APPLICATOR

SPARKS OF NEW TECHNOLOGY MECH-SENSOR WITH STRIKING NOVELTY

## THE LABELLING STROKE IS UP TO 55mm.

No other conventional type label applicators assures proper and exact labelling like the AP65 series of TOWA LABEL APPLICATOR.



The **Mech-Sensor** adjusts label strokes automatically.



AP65-30



AP65-60



AP65-100

### HOW TO USE

1

Open Label Holder, place label roll, push down Bottom Lever to open.




2

Insert label sideways under transparent Label Pressor, turn it back onto Bottom Cover, then close Label Holder.



3

Close Bottom Cover, lock it firmly with Bottom Lever.



4

Cut backing paper, pulling it downwards carefully as arrow indicates.



5

Pull machine toward you at the same speed with gripping motion.



### NOTICE

1. Unnecessary to make feedslots on backing paper.
2. Use only die-cut labels. Less than 50μm thickness labels and synthetic paper labels may not be dispensed.
3. The backside form of label roll and blue color backing paper is recommended.
4. A cotton-swab moistened with **Ethyl-ALCOHOL** is recommended to wipe adhesive from Mech-Sensor.

### SPECIFICATIONS

MODEL	LABEL SIZE (mm)		MAX. OUTSIDE DIAMETER (mm)
	STROKE	WIDTH	
AP65-30	20-55	20-30	100
AP65-60	20-55	25-60	100
AP65-100	20-55	50-100	100

Please contact us if your shape labels seem difficult to dispense.

\*We reserve the right to change specifications without notice for improvement.

## TOWA COMPANY, LIMITED

Ginza YK Bldg., No. 10-9, Ginza 5-chome, Chuo-ku, Tokyo 104-0061, Japan  
Tel: 81-3-3572-9621, Fax: 81-3-3572-9620  
<http://www.towa-jp.com>